








Ordering Information:

A2541WR-XP - \*\*\* - \*\*\* - \*  
1 2 3 4

- 1.Part No.
- 2.Size(H):  
(blank): 2.54mm  
H15: 1.50mm  
H17: 1.70mm  
H20: 2.00mm  
H30: 3.00mm
- 3.Material:  
(blank): PBT,UL94V-0  
6T: Nylon 6T,UL94V-0  
GWT: Nylon 6T,UL94V-0,GWT 750°C
- 4.Finish:  
(blank): Gold over Nickel  
T: Tin over Nickel



P.C.B LAYOUT



SPECIFICATIONS:

Current Rating: 3A AC,DC  
Voltage Rating: 250V AC,DC  
Temperature Range: -40°C ~ +105°C  
Contact Resistance: 20mΩ Max  
Insulation Resistance: 1000MΩ Min  
Withstanding Voltage: 1500V AC/minute  
Pin Material:Brass/Gold over Nickel  
Material:PBT ,UL94V-0(Black)

Ordering Information & Dimensions

Circuits	Dim(mm)		Circuits	Dim(mm)		Circuits	Dim(mm)	
	A	B		A	B		A	B
2P	2.54	5.08	15P	35.56	38.10	28P	68.58	71.12
3P	5.08	7.62	16P	38.10	40.64	29P	71.12	73.66
4P	7.62	10.16	17P	40.64	43.18	30P	73.66	76.20
5P	10.16	12.70	18P	43.18	45.72	31P	76.20	78.74
6P	12.70	15.24	19P	45.72	48.26	32P	78.74	81.28
7P	15.24	17.78	20P	48.26	50.80	33P	81.28	83.82
8P	17.78	20.32	21P	50.80	53.34	34P	83.82	86.36
9P	20.32	22.86	22P	53.34	55.88	35P	86.36	88.90
10P	22.86	25.40	23P	55.88	58.42	36P	88.90	91.44
11P	25.40	27.94	24P	58.42	60.96	37P	91.44	93.98
12P	27.94	30.48	25P	60.96	63.50	38P	93.98	96.52
13P	30.48	33.02	26P	63.50	66.04	39P	96.52	99.06
14P	33.02	35.56	27P	66.04	68.58	40P	99.06	101.60

深圳市金航标电子有限公司      WWW.BDS666.COM  
KH-A2541WR-14P      0755-83044319

Unit mm	Scale 4:1	Sheet 1 of 1	Title : <b>2.54mm Pitch</b>	
Draw By: Diankui Wan		Approved : Jack Yin		<b>90° Single Row Pin Header</b>
General Tolerance				
A2 CHANGE THE TOLERANCE 2019.09.06		A1 updated version 2018.03.30		DRAW NO : <b>A2541WR-XP</b> REV <b>A2</b>
A0 NEW RELEASE 2005.07.01		REV DESCRIPTION DATE		

A2	CHANGE THE TOLERANCE	2019.09.06	x.xx±0.25 x.xxx±0.15	PROJECT ⊕
A1	updated version	2018.03.30		
A0	NEW RELEASE	2005.07.01		
REV	DESCRIPTION	DATE		