


环保物料



TEL: 0769-82001899

TABLE :

| N  | A  | B    | C    |
|----|----|------|------|
| 4  | 3  | 5.1  | 7.0  |
| 5  | 4  | 6.1  | 8.0  |
| 6  | 5  | 7.1  | 9.0  |
| 7  | 6  | 8.1  | 10.0 |
| 8  | 7  | 9.1  | 11.0 |
| 9  | 8  | 10.1 | 12.0 |
| 10 | 9  | 11.1 | 13.0 |
| 11 | 10 | 12.1 | 14.0 |
| 12 | 11 | 13.1 | 15.0 |
| 13 | 12 | 14.1 | 16.0 |
| 14 | 13 | 15.1 | 17.0 |
| 15 | 14 | 16.1 | 18.0 |
| 16 | 15 | 17.1 | 19.0 |
| 17 | 16 | 18.1 | 20.0 |
| 18 | 17 | 19.1 | 21.0 |
| 19 | 18 | 20.1 | 22.0 |
| 20 | 19 | 21.1 | 23.0 |
| 21 | 20 | 22.1 | 24.0 |
| 22 | 21 | 23.1 | 25.0 |
| 23 | 22 | 24.1 | 26.0 |
| 24 | 23 | 25.1 | 27.0 |
| 25 | 24 | 26.1 | 28.0 |
| 26 | 25 | 27.1 | 29.0 |
| 27 | 26 | 28.1 | 30.0 |
| 28 | 27 | 29.1 | 31.0 |
| 29 | 30 | 30.1 | 32.0 |
| 30 | 29 | 31.1 | 33.0 |
| 31 | 30 | 32.1 | 34.0 |
| 32 | 31 | 33.1 | 35.0 |
| 33 | 32 | 34.1 | 36.0 |
| 34 | 33 | 35.1 | 37.0 |
| 35 | 34 | 36.1 | 38.0 |



适用FFC寸法  
Applicable FFC



PCB 寸法  
PCB Layout

F1006VS-ZV-xx-34T-x

R=卷装 无=管装  
T=镀锡 G=镀金  
Pin位数  
ZV=正脚位 FV=反脚位

额定电流 Current rating: 0.5A  
额定电压 Voltage rating: 125V  
耐电压 Withstand coltage: 500V AC/minute  
接触电阻 Contact resistance :  $\leq 30m\Omega$   
绝缘电阻 Insulation resistance: 500M $\Omega$   
工作温度 Working temperature: -20 $^{\circ}c \sim +80^{\circ}c$

BOM 表 :

| 2  | 1.0mm间距B型单面接立式-PIN |    | PhosphorBronze T=0.25MM | 镀锡      | 1SET  | 1Set = N POS |    |
|----|--------------------|----|-------------------------|---------|-------|--------------|----|
| 1  | 1.0mm间距B型单面接-基座    |    | SEE TABLE SEE TABLE 1   | 本色      | 1 PCS |              |    |
| 序号 | 品名                 | 料号 | 材料规格                    | 电镀方式/颜色 | 使用数量  | 备注           | 版本 |

TOLERANCE UNLESS OTHERWISE

|      |            |                 |                   |
|------|------------|-----------------|-------------------|
| X.   | $\pm 0.30$ | X $^{\circ}$    | $\pm 5^{\circ}$   |
| .X   | $\pm 0.20$ | .X $^{\circ}$   | $\pm 2^{\circ}$   |
| .XX  | $\pm 0.08$ | .XX $^{\circ}$  | $\pm 1^{\circ}$   |
| .XXX | $\pm 0.03$ | .XXX $^{\circ}$ | $\pm 0.5^{\circ}$ |

DRAWN CK tan

|      |  |
|------|--|
| CHKD |  |
| APPD |  |
| VIEW |  |

**XFCN** 兴飞连接器有限公司  
XFCN CONNECTORS CO.,LTD.

PRODUCT NAME FPC 1.00mm Connectors

PART. NO. F1006VS-ZV-xx-34T-R

SHEET 1/1

DATE 2020.04.12

UNITS mm

SCALE 1:1

DWG. NO. 009

AO  
VER

MODIFICATION

DRAW

DATE

1 2 3 4 5 6 7 8 9 10