



SPECIFICATIONS

- 1、Current Rating: 9A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
5557-2*1AW		5.40
5557-2*2AW	4.20	9.60
5557-2*3AW	8.40	13.80
5557-2*4AW	12.60	18.00
5557-2*5AW	16.80	22.20
5557-2*6AW	21.00	26.40
5557-2*7AW	25.20	30.60
5557-2*8AW	29.40	34.80
5557-2*9AW	33.60	39.00
5557-2*10AW	37.80	43.20
5557-2*11AW	42.00	47.40
5557-2*12AW	46.20	51.60

PCB LAYOUT

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013.07.01	料号 PART NO.	5557-2*NA	版本 REV.	A
			X. \pm 0.25	X. \pm 2°	审核 CHECK	张名 2013.07.03	品名 TITLE	双排弯针 WAFER DIP TYPE	页次 SHEET	1/1
			.X \pm 0.20	.X \pm 1°	核准 APPROVAL	张名 2013.07.05	客户料号 CUTL. NO.		富港电子	
			.XX \pm 0.15	.XX \pm 0.5°	单位 UNITS	MM	比例 SCALE	1:1		
			.XXX \pm 0.10	.XXX \pm 0.5°						