



SPECIFICATIONS

- 1、Current Rating: 9A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
5557-2*1AW		5.40
5557-2*2AW	4.20	9.60
5557-2*3AW	8.40	13.80
5557-2*4AW	12.60	18.00
5557-2*5AW	16.80	22.20
5557-2*6AW	21.00	26.40
5557-2*7AW	25.20	30.60
5557-2*8AW	29.40	34.80
5557-2*9AW	33.60	39.00
5557-2*10AW	37.80	43.20
5557-2*11AW	42.00	47.40
5557-2*12AW	46.20	51.60

PCB LAYOUT

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	5557-2*NA		版本 REV.	A				
			X.±0.25	X.'±2'		审核 CHECK	2013、07、01		品名 TITLE	双排弯针		页次 SHEET	1/1			
			.X±0.20	.X'±1'			核准 APPROVAL			张名			客户料号 CUTM. NO.	WAFER DIP TYPE		
			.XX±0.15	.XX'±0.5'						张名				富 港 电 子		
.XXX±0.10	.XXX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1											