



SPECIFICATIONS

- 1、Current Rating: 9A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated



编 号	尺寸 (mm)	
	A	B
5557-2*1A		5.40
5557-2*2A	4.20	9.60
5557-2*3A	8.40	13.80
5557-2*4A	12.60	18.00
5557-2*5A	16.80	22.20
5557-2*6A	21.00	26.40
5557-2*7A	25.20	30.60
5557-2*8A	29.40	34.80
5557-2*9A	33.60	39.00
5557-2*10A	37.80	43.20
5557-2*11A	42.00	47.40
5557-2*12A	46.20	51.60

PCB LAYOUT

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	5557-2*NA		版本 REV.	A				
			X.±0.25	X.*±2'		2013、07、01	张名		品名 TITLE	双排直针		页次 SHEET	1/1			
			.X±0.20	.X*±1'						2013、07、03			张名	客户料号 CUTL NO.	WAFER DIP TYPE	
			.XX±0.15	.XX*±0.5'											2013、07、05	富港电子
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1			富港电子								