



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0  
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
VH-2A2W-G	3.96	7.92
VH-3A3W-G (VH-3A2W-G)	7.92	11.88
VH-4A4W-G	11.88	15.84
VH-5A5W-G	15.84	19.80
VH-6A6W-G	19.80	23.76
VH-7A7W-G	23.76	27.72
VH-8A8W-G	27.72	31.68
VH-9A9W-G	31.68	35.64
VH-10A10W-G	35.64	39.60
	39.60	43.56
	43.56	47.52

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	VH-NANW-G		版本 REV.	A	
			X.±0.25	X.*±2'		审核 CHECK	2013、07、01		VH高弯			页次 SHEET	1/1
			.X±0.20	.X*±1'			2013、07、03		WAFER DIP TYPE				
			.XX±0.15	.XX*±0.5'			核准 APPROVAL		张名	客户料号 CUTL. NO.			富港电子
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1								