



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

| 编 号 | 尺寸 (mm) | |
|-----------------------|---------|-------|
| | A | B |
| VH-2A2W-G | 3.96 | 7.92 |
| VH-3A3W-G (VH-3A2W-G) | 7.92 | 11.88 |
| VH-4A4W-G | 11.88 | 15.84 |
| VH-5A5W-G | 15.84 | 19.80 |
| VH-6A6W-G | 19.80 | 23.76 |
| VH-7A7W-G | 23.76 | 27.72 |
| VH-8A8W-G | 27.72 | 31.68 |
| VH-9A9W-G | 31.68 | 35.64 |
| VH-10A10W-G | 35.64 | 39.60 |
| | 39.60 | 43.56 |
| | 43.56 | 47.52 |

| | | | | | | | | | | | | | | | |
|-------------|---------------------|-------------|-------------------|-----------|---------------|------------|----|----------------|-----------|-------------|------------|-----|------------|-------------------|----------------|
| 制图 DRAWN | 变更内容 DESCRIPTION | 日期 DATE | GENERAL TOLERANCE | | 制图 DRAWING | 钱岳生 | | 料号 PART NO. | VH-NANW-G | | 版本 REV. | A | | | |
| | | | X.±0.25 | X.*±2' | | 2013、07、01 | 张名 | | VH高弯 | 页次 SHEET | | 1/1 | | | |
| | | | .X±0.20 | .X*±1' | | | | | | | | | 2013、07、03 | 张名 | WAFER DIP TYPE |
| | | | .XX±0.15 | .XX*±0.5' | | | | | | | | | 张名 | 客户料号 CUTL. NO. | |
| .XXX±0.10 | .XXX*±0.5' | 2013、07、05 | 张名 | 富港电子 | | | | | | | | | | | |
| 单位 UNITS | MM | 比例 SCALE | 1:1 | | | | | | | | | | | | |