



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer LCP、PA6T,UL94V-0
PIN Brass Tin-plated
Solder tad Phosphoric bronze Tin-plated

编 号	尺寸 (mm)		
	A	B	C
HA-2ALT	2.50	10.00	7.50
HA-3ALT	5.00	12.50	10.00
HA-4ALT	7.50	15.00	12.50
HA-5ALT	10.00	17.50	15.00
HA-6ALT	12.50	20.00	17.50
HA-7ALT	15.00	22.50	20.00
HA-8ALT	17.50	25.00	22.50
HA-9ALT	20.00	27.50	25.00
HA-10ALT	22.50	30.00	27.50
HA-11ALT	25.00	32.50	30.00
HA-12ALT	27.50	35.00	32.50

PCB LAYOUT

GENERAL TOLERANCE		制 图	钱岳生		料 号	HA-NALT		版 本	A
X.±0.25	X.'±2'	DRAWING	2017、06、01		PART NO.			REV.	
.X±0.20	.X'±1'	审 核	张 名		品 名	HA立贴		页 次	1/1
.XX±0.15	.XX'±0.5'	CHECK	2017、06、03		TITLE	WAFER SMT TYPE		SHEET	
.XXX±0.10	.XXX'±0.5'	核 准	张 名		客 户 料 号				
		APPROVAL	2017、06、05		CUTL. NO.				
		单 位	MM	比 例	1:1		富 港 电 子		
		UNITS	SCALE						