



**SPECIFICATIONS**

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer LCP,UL94V-0  
PIN Brass Tin-plated  
Solder tad Brass Tin-plated

编号	尺寸 (mm)		
	A	B	C
HA-2AWT	2.50	7.50	10.00
HA-3AWT	5.00	10.00	12.50
HA-4AWT	7.50	12.50	15.00
HA-5AWT	10.00	15.00	17.50
HA-6AWT	12.50	17.50	20.00
HA-7AWT	15.00	20.00	22.50
HA-8AWT	17.50	22.50	25.00
HA-9AWT	20.00	25.00	27.50
HA-10AWT	22.50	27.50	30.00
HA-11AWT	25.00	30.00	32.50
HA-12AWT	27.50	32.50	35.00

**PCB LAYOUT**

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013、07、01	料号 PART NO.	HA-NAWT		版本 REV.	A
			X.±0.25	X.'±2'	审核 CHECK	张名 2013、07、03	品名 TITLE	HA贴片 WAFER SMT TYPE		页次 SHEET	1/1
			.XX±0.15	.XX'±0.5'	核准 APPROVAL	张名 2013、07、05	客户料号 CUTL. NO.				
			.XXX±0.10	.XXX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1	<b>富港电子</b>		