



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer LCP, UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
HY-2AWT	2.00	8.00
HY-3AWT	4.00	10.00
HY-4AWT	6.00	12.00
HY-5AWT	8.00	14.00
HY-6AWT	10.00	16.00
HY-7AWT	12.00	18.00
HY-8AWT	14.00	20.00
HY-9AWT	16.00	22.00
HY-10AWT	18.00	24.00
HY-11AWT	20.00	26.00
HY-12AWT	22.00	28.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制 图 DRAWING	钱岳生		料 号 PART NO.	HY-NAWT		版 本 REV.	A				
			X.±0.25	X.*±2'		2013、07、01	部 名 TITLE		HY贴片	页 次 SHEET			1/1			
			.X±0.20	.X*±1'										2013、07、03	客 户 料 号 CUTM. NO.	
			.XX±0.15	.XX*±0.5'												核 准 APPROVAL
.XXX±0.10	.XXX*±0.5'	单 位 UNITS	MM	比 例 SCALE	1:1											
富 港 电 子																