



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer LCP, UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
HY-2AWT	2.00	8.00
HY-3AWT	4.00	10.00
HY-4AWT	6.00	12.00
HY-5AWT	8.00	14.00
HY-6AWT	10.00	16.00
HY-7AWT	12.00	18.00
HY-8AWT	14.00	20.00
HY-9AWT	16.00	22.00
HY-10AWT	18.00	24.00
HY-11AWT	20.00	26.00
HY-12AWT	22.00	28.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	HY-NAWT		版本 REV.	A		
			X.±0.25	X.*±2'		2013、07、01	品名		HY贴片	页次 SHEET			1/1	
			.X±0.20	.X*±1'		审核	张名		客户料号					富港电子
			.XX±0.15	.XX*±0.5'		2013、07、03	张名		CUTL. NO.					
.XXX±0.10	.XXX*±0.5'	核准	张名	2013、07、05	单位	MM	比例	1:1	富港电子					