


REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	20.05.19	Mark
A1	变更天线结构	20.06.19	Mark

胶帽点胶水固定，注意胶水不要溢出来



No.	PART NUMBER	PART NAME & DESCRIPTION	Q'TY	REMARKS
5	2SBKG5701	SR 黑色, OD:6.6*L15.9mm	1	---
4	2SBKG5401	黑色硅胶帽, OD:5.0*ID2.9*L12.0mm	1	---
3	2TA025BK0-000	OD:2.5*L168.0, 黑色普通热缩套管	1	---
2	2YT075	5层铜材弹性线, OD:2.85*L173.5mm	1	---
1	2LC15PM062	SMA 黄铜镀金, H8.0*L19.6mm	1	---

GENERAL TOLERANCE:		HJ-Tech 东莞市皇捷通讯科技有限公司	
LINEAR:		手机: 15015262131/13714786106	
X	±1.00	FILE NAME:	产品图
X.X	±0.50	ENG/DATE:	Mark/20.05.19
X.XX	±0.30	CHE/DATE:	
X.XXX	±0.20	APP/DATE:	
ANGLE:		TITLE: 射频天线组件	
X°	±4.00°	SMA PLUG Flexible antenna (434MHz)	
X.X°	±3.00°	P/N: 434MHz-SMA Flexible antenna	
X.XX°	±2.00°	UNIT:	mm
X.XXX°	±1.00°	SCALE:	1:1
		REVISION:	A0
		SHEET:	1/1

技术要求:

1 电气特性:

特性阻抗:50Ω; 适用频率范围:434MHz;

2 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。

3 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污;

镀层色泽光亮均匀, 不得有氧化。

4 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □ HF; □ SONY SS-00259; □ OTHERS
*NO USING ESTRICTED AND BANNED SUBSTANCE

H005