






SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au3U Over Ni
 Insulator Material:Polyester(UL94V-0) PBT Black
 Max.Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)

SQ PIN:0.64x11.5mm



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司	
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.		BH-00022	
A0	2014.04.16	NEW DRAWING		X.XXX	±0.10	APPROVE		SHEET	1/1	TITLE:		2.54 BOX 2X10P PC3.3 AU3U PBT DIP	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	ANGLE	DIM		TOL	PROJ.				
1	2	3	4	5	6	7	8	9					