




RoHS

SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ± 0.05)

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
OPERATION	UNIT	CHECK	UNIT	UNIT	mm	UNIT	mm	SIZE	SHEET
X.X	±0.30							A4	1/1
X.XX	±0.20								
X.XXX	±0.10								
Angle	±3°								
DIM	TOL	APPROVE		PROJ.					

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1	2012.03.28	NEW DRAWING	

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1	2012.03.28	NEW DRAWING	

TITLE:	PART NO.
2.54Box 20P H8.8mm 180°	BH-00063