


RoHS




SPECIFICATIONS

Rated Current:1.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Phosphor Bronze  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



W= With Post

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司	
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.		FH-00185	
				X.XXX	±0.10			SHEET	1/1	TITLE:		1.27FH 2x13Pin H4.3 SMT 连接器	
				Angle	±3°	APPROVE		PROJ.	◆				
				DIM	TOL								
REV	DATE	MODIFICATION DESCRIPTION		CHANGE									
1	2012.04.18	NEW DRAWING											