





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c
Contact Material:Brass
Contact Plating:Au Or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp.: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



深圳市连盛精密连接器有限公司

PART NO. **FH-00522**

TITLE: 2.54FH=8.5 W=5.0 2x4P 空第3-6P
DIP PC2.1 Y型 AU1U 青铜 PA6T

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	SCALE		FIT	PART NO.	TITLE:
				X.XX	±0.30		UNIT	mm			
A0	2012.03.28	NEW DRAWING		X.XX	±0.20	CHECK	SIZE	A4			
				X.XXX	±0.10		SHEET	1/1			
				Angle	±3°	APPROVE	PROJ.				
				DIM	TOL						