





ROHS

SPECIFICATIONS

Rated Current: 1.5AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C
 Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)



Dimension antitheses list			
ITEM	PC	PA	L
Standard	2.80	3.90	8.70
Alternate			

深圳市连盛精密连接器有限公司

PART NO. PH-00105

TITLE: 2.0PH H=2.0 2x5P DIP PA3.9
 PC2.8 L=8.7 AU0.8U PA6T

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30	X.XX	±0.20	UNIT	mm	SIZE	A4
X.XXX	±0.10	CHECK		SIZE		SHEET	1/1
Angle	±3°	APPROVE		PROJ.			
DIM	TOL						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.04.11	NEW DRAWING	
1			