





RoHS

SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PC	PA	L
Standard	2.80	3.90	8.70
Alternate			

深圳市连盛精密连接器有限公司

PART NO.

PH-00121

TITLE:

2.0PH 2x40pin H2.0mm DIP PA3.9
 PC2.8

OPERATION

DRAW

SCALE

FIT

X.X ±0.30

UNIT

mm

X.XX ±0.20

CHECK

SIZE

A4

X.XXX ±0.10

APPROVE

SHEET

1/1

Angle ±3°

PROJ.

PROJ.

PROJ.

REV A0

DATE 2012.04.11

MODIFICATION DESCRIPTION NEW DRAWING

1

2

3

4

5

6

7

8

9