



品赞科技

SwitcH

技术规格:

1.电气特性:

耐压:100V AC/60S/0.5mA;
 绝缘阻抗: 100MΩ/MIN,500V DC/MIN;
 接触阻抗: 40mΩ/MAX(VBUS/GND),测试后变化10mΩ;
 额定电流: 2A 温度:30°/MAX;

2.机械特性:

插入力: 5~20N;
 拔出力: 8~20N,测试后拔出力6~20N;
 耐久次数:1000次;

3.标示 为重点尺寸,首件必须检测;标示 为FAI尺寸;

4.使用物料及制程符合“GP”文件对环境物料管理标准.

PIN DEFINE:

Pin	Signal Name	Description	Mating Sequence	Pin	Signal Name	Description	Mating Sequence
A1	GND	Ground return	First	B4	GND	Ground return	First
A4	Vbus	Bus Power	First	B1	Vbus	Bus Power	First



G-Switch Electronic (HongKong) CO.,Ltd.

Unless otherwise specified, Tolerance:
 X. ±0.30
 X.x ±0.20
 X.xx ±0.15
 X.xxx ±0.10
 Angles ±3°

DESIGN FengFengChen DATE 2021.02.01
 CHECKED DATE
 APPROVED DATE
<http://www.dg-switch.com>
 TEL:0769-82388879

Molde code:
GT-USB-7063
 REV.: X1 SCALE: 4:1 UNIT: mm
 SIZE: A4 SHEET: 1/1