

## SPECIFICATIONS



Rated Current: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C

Contact Material: Brass  
 Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PBT

Max. Processing Temp: 180°C for 30-60 seconds  
 (200°C for 10 seconds)




## Ordering Information

3210- XX S XX X BK00 X 01

No. of Pins Per Row 6--64	Contact Plating G0: Gold Flash G1: 3U" Gold G2: 5U" Gold G3: 10U" Gold G4: 15U" Gold G5: 30U" Gold SN: Tin	Insulator Material Option A=BK-PBT B=BK-PA66 C=BK-PA6T D=BK-PA46 F=BK-LCP	Packing 0=PE Bog A=Tray T=Tube P=Tube+Cap
------------------------------	---	--	---

Recommended P.C.B Layout (Top Side)  
 (PCB BOARD TOLERANCE ± 0.05)



深圳市连盛精密连接器有限公司

PART NO. BH-00055

TITLE: 2.54Box 16P H8.8mm 180°

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30	X.X	±0.30	UNIT	mm		
X.XX	±0.20	CHECK		SIZE	A4		
X.XXX	±0.10	Angle	±3°	SHEET	1/1		
DIM	TOL	APPROVE		PROJ.			
OPERATION		DRAW		SCALE		FIT	
DRAW		CHECK		UNIT		mm	
CHECK		APPROVE		SIZE		A4	
APPROVE		TITLE:		SHEET		1/1	
TITLE:		PART NO.		PROJ.			
2.54Box 16P H8.8mm 180°		BH-00055					

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.03.28	NEW DRAWING	
1			