





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



料号 : PH-00244

2X5P

| Dimension antitheses list | | | |
|---------------------------|------|------|-------|
| ITEM | PA | PC | L |
| Standard | 6.00 | 3.00 | 11.50 |
| Alternate | | | |

深圳市连盛精密连接器有限公司

PART NO. PH-00244

TITLE: 2.54PH H2.5mm 2xNP 180°

| REV | DATE | MODIFICATION DESCRIPTION | CHANGE | OPERATION | | DRAW | SCALE | FIT |
|-----|------------|--------------------------|--------|-----------|-------|---------|-------|-----|
| | | | | X.X | ±0.30 | | | |
| A0 | 2012.03.28 | NEW DRAWING | | X.XX | ±0.20 | CHECK | UNIT | mm |
| | | | | X.XXX | ±0.10 | APPROVE | SIZE | A4 |
| | | | | Angle | ±3° | | SHEET | 1/1 |
| | | | | DIM | TOL | | PROJ. | ☐ |