




RoHS

SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C
 Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



深圳市连盛精密连接器有限公司

| OPERATION | | DRAW | | SCALE | | FIT | | PART NO. | |
|--|-------|---------|--|-------|-----|-----|--|---------------------------------|--|
| X.X | ±0.30 | | | UNIT | mm | | | PH-00266 | |
| X.XX | ±0.20 | CHECK | | SIZE | A4 | | | 2.54PH 2H=2x2.5 2X10P DIP PA6.5 | |
| X.XXX | ±0.10 | | | SHEET | 1/1 | | | PC2.5 L=14.5 PA6T | |
| Angle | ±3° | APPROVE | | PROJ. | | | | | |
| DIM | TOL | | | | | | | | |
| <p>1 2 3 4 5 6 7 8 9</p> | | | | | | | | | |
| <p>REV 1 DATE 2012.03.28 MODIFICATION DESCRIPTION NEW DRAWING CHANGE</p> | | | | | | | | | |