







SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard:

Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	6.00	4.20	3.00	13.80
Alternate				

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司 PART NO. PH-00323 TITLE: 2.54PH H=2.5 1XNP 正弯 PA6.0 PC3.0	
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4				
A0				2012.07.02	NEW DRAWING			SHEET	1/1				
REV	DATE	MODIFICATION	DESCRIPTION	CHANGE	DIM	TOL	APPROVE	PROJ.					
1	2	3	4	5	6	7	8	9					