





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:AU3U Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list					
ITEM	PC	PB	PA	L	TYPE
Standard	3.00	8.12	3.00	14.12	Type01
Alternate					

深圳市连盛精密连接器有限公司

PART NO.

PH-00405

TITLE:

2.54PH 2H=2X2.50 1X20P
 PA=PC=3.0 PB=8.12 PA6T

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

CHECK

APPROVE

SCALE

UNIT

SIZE

SHEET

PROJ.

FIT

mm

A4

1/1

◆

A0 2014.04.16 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION

CHANGE

1 2 3 4 5 6 7 8 9