







SPECIFICATIONS

- 1、 Current Rating: 3A AC, DC
- 2、 Voltage Rating: 250V AC, DC
- 3、 Temperatuer Range: -25°C~+85°C
- 4、 Contact Resistance: 30mΩ Max
- 5、 Insulation Resistance: 1000MΩ Min
- 6、 Withstanding Voltang: 800V AC/minute
- 7、 Material: Wafer PA66, Beige UL94V-0
PIN Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
XHD-2*2AW	2.50	7.50
XHD-2*3AW	5.00	10.00
XHD-2*4AW	7.50	12.50
XHD-2*5AW	10.00	15.00
XHD-2*6AW	12.50	17.50
XHD-2*7AW	15.00	20.00
XHD-2*8AW	17.50	22.50
XHD-2*9AW	20.00	25.00
XHD-2*10AW	22.50	27.50
XHD-2*11AW	25.00	30.00
XHD-2*12AW	27.50	32.50

GENERAL TOLERANCE	制 图	钱岳生	料 号	XHD-2*NAW	版 本	A
X.X±0.25 X.'±2'	DRAWING	2016、09、22	PART NO.		REV.	
X.XX±0.20	审 核	张 名	品 名	XHD2.5弯针	页 次	1/1
X.XXX±0.10	CHECK	2016、09、23	TITLE	WAFER DIP TYPE	SHEET	
	核 准	张 名	客 户 料 号			
	APPROVAL	2016、09、24	CUTL. NO.			
	单 位	MM	比 例	富 港 电 子		
	UNITS		SCALE	1:1		