



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material:Wafer Nylon66, UL94V-0
PIN Brass(H65) Tin-plated

编 号	尺寸 (mm)		
	A	B	C
PHB-2*2AW	2.00	6.00	3.00
PHB-2*3AW	4.00	8.00	3.00
PHB-2*4AW	6.00	10.00	3.00
PHB-2*5AW	8.00	12.00	5.00
PHB-2*6AW	10.00	14.00	7.00
PHB-2*7AW	12.00	16.00	9.00
PHB-2*8AW	14.00	18.00	11.00
PHB-2*9AW	16.00	20.00	13.00
PHB-2*10AW	18.00	22.00	15.00
PHB-2*11AW	20.00	24.00	17.00
PHB-2*12AW	22.00	26.00	19.00
PHB-2*13AW	24.00	28.00	21.00
PHB-2*14AW	26.00	30.00	23.00
PHB-2*15AW	28.00	32.00	25.00
PHB-2*16AW	30.00	34.00	27.00
PHB-2*17AW	32.00	36.00	29.00
PHB-2*18AW	34.00	38.00	31.00
PHB-2*19AW	36.00	40.00	33.00
PHB-2*20AW	38.00	42.00	35.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生	料号 PART NO.	PHB-2*NAW	版本 REV.	A		
			X.±0.25	X.*±2'		2013、07、01		品名 TITLE		PHB直针	页次 SHEET	1/1
			.X±0.20	.X*±1'		审核 CHECK		张名		WAFER DIP TYPE	客户料号 CUTL. NO.	
			XX+0.15	XX'+0.5'		核准 CHECK		张名		1:1		
联系电话 18058866958						深圳市华灿天禄电子有限公司						

联系电话 18058866958

深圳市华灿天禄电子有限公司