



TYPE 1



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 500MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer PBT, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
ZH1.5-2A	1.50	4.50
ZH1.5-3A	3.00	6.00
ZH1.5-4A	4.50	7.50
ZH1.5-5A	6.00	9.00
ZH1.5-6A	7.50	10.50
ZH1.5-7A	9.00	12.00
ZH1.5-8A	10.50	13.50
ZH1.5-9A	12.00	15.00
ZH1.5-10A	13.50	16.50
ZH1.5-11A	15.00	18.00
ZH1.5-12A	16.50	19.50
ZH1.5-13A	18.00	21.00
ZH1.5-14A	19.50	22.50
ZH1.5-15A	21.00	24.00
ZH1.5-16A	22.50	25.50

联系电话 18058866958

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	ZH1.5直针		版本 REV.	A
			X.±0.25	X.*±2'		2013.07.01	品名 TITLE		ZH直针	页次 SHEET		1/1
			.X±0.20	.X*±1'		审核 CHECK	2013.07.03		客户料号 CUTL. NO.			
			.XX±0.15	.XX*±0.5'		核准 APPROVAL	张名		深圳市华灿天禄电子有限公司			
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1							