



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $100\text{M}\Omega$ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon46, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
1.25-2A	1.25	4.25
1.25-3A	2.50	5.50
1.25-4A	3.75	6.75
1.25-5A	5.00	8.00
1.25-6A	6.25	9.25
1.25-7A	7.50	10.50
1.25-8A	8.75	11.75
1.25-9A	10.00	13.00
1.25-10A	11.25	14.25
1.25-11A	12.50	15.50
1.25-12A	13.75	16.75
1.25-13A	15.00	18.00
1.25-14A	16.25	19.25
1.25-15A	17.50	20.50
1.25-16A	18.75	21.75

联系电话 18058866958

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	1.25-NA		版本 REV.	A			
			X. \pm 0.25	X.* \pm 2'		审核 CHECK	2013、07、01		品名 TITLE	1.25开口直针		页次 SHEET	1/1		
			.X \pm 0.20	.X* \pm 1'			2013、07、03			WAFER DIP TYPE					
			.XX \pm 0.15	.XX* \pm 0.5'			张名			客户料号 CUTL NO.					
.XXX \pm 0.10	.XXX* \pm 0.5'	张名													
单位 UNITS			MM	比例 SCALE	1:1	深圳市华灿天禄电子有限公司									