





RoHS

SPECIFICATIONS

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°c to +105°c

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list					
ITEM	PC	PB	PA	L	TYPE
Standard	3.00	8.00	3.00	14.00	Type01
Alternate					

深圳市连盛精密连接器有限公司

PART NO.

PH-00294

TITLE:

2.54PH 2H=2X2.5 1X3P

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	SCALE	FIT
				X.X	±0.30			
A0	2014.04.16	NEW DRAWING		X.XX	±0.20	CHECK	UNIT	mm
				X.XXX	±0.10		SIZE	A4
				Angle	±3°	APPROVE	SHEET	1/1
				DIM	TOL		PROJ.	☐