


尺寸	X	Y
0.75~1.25	19.2-0.1	13.0+0.1
1.25~2.00	19.4-0.1	13.0+0.1
2.00~3.00	19.8-0.1	13.0+0.1

CUT-OUT

MATERIAL:
 Cover: Nylon66, UL rated: 94V-2 min
 Base: Nylon66, UL rated: 94V-2 min
 Terminal: Brass, silver or tin plated
 Rating: 10A 125V AC (UL CUL)
 6A 250V AC (UL CUL VDE CE CQC)
 Function: ON-OFF
 Contact Resistance: 50mΩ Max
 Insulation Resistance: DC 500V 100MΩ Min
 Dielectric Strength: AC1500V 1 minute
 Electrical life: 10,000 cycles
 Operating Temperature: -20℃~85℃
 Safety Approval:



公差 TOLERANCES .X± 0.5 .XX± 0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	核对 CHECKED BY	日期 DATE	品名 TITLE	图号 DRAWING NO
A 1	整理图面	2020.07.10				2020.07.10	MR-2-110-C2N-BB	MR-2-110-C2N-BB_A0