



尺寸	X	Y
0.75~1.25	19.2-0.1	13.0+0.1
1.25~2.00	19.4-0.1	13.0+0.1
2.00~3.00	19.8-0.1	13.0+0.1

**MATERIAL:**

Cover: Nylon66, UL rated: 94V-2 min  
 Base: Nylon66, UL rated: 94V-2 min  
 Terminal: Brass, silver or tin plated  
 Rating: 10A 125V AC (UL CUL )  
 6A 250V AC (UL CUL VDE CE CQC)  
 Function: ON-OFF  
 Contact Resistance: 50mΩ Max  
 Insulation Resistance: DC 500V 100MΩ Min  
 Dielectric Strength: AC3000V 1 minute  
 Electrical life: 10,000 cycles  
 Operating Temperature: 0℃~85℃  
 Safety Approval:

**CUT-OUT**



**D · SWITCH**  
 东莞市德松电子有限公司  
 D-SWITCH ELECTRONICS CO.,LTD

公差 TOLERANCES .X±0.5 .XX±0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	比例尺 SCALE	日期 DATE	品名 TITLE	图号 DRAWING NO
					1:1	2019.01.08	MR-2-210-C5L-BR220	MR-2-210-C5L-BR220_A0