



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
HY-2A	2.00	6.00
HY-3A	4.00	8.00
HY-4A	6.00	10.00
HY-5A	8.00	12.00
HY-6A	10.00	14.00
HY-7A	12.00	16.00
HY-8A	14.00	18.00
HY-9A	16.00	20.00
HY-10A	18.00	22.00
HY-11A	20.00	24.00
HY-12A	22.00	26.00
HY-13A	24.00	28.00
HY-14A	26.00	30.00
HY-15A	28.00	32.00
HY-16A	30.00	34.00

联系电话 18058866958

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	HY-NA		版本 REV.	A			
			X.±0.25	X.*±2'		审核 CHECK	2013、07、01		品名 TITLE	HY直针		页次 SHEET	1/1		
			.X*±0.20	.X*±1'			核准 APPROVAL			2013、07、03			客户料号 CUTL. NO.	WAFER DIP TYPE	
			.XX±0.15	.XX*±0.5'						张名					
.XXX±0.10	.XXX*±0.5'	张名	2013、07、05				深圳市华灿天禄电子有限公司								
单位 UNITS	MM	比例 SCALE	1:1												