



Nut Torque: 5 ~ 14Nm
 Operating Pressure: 400gf ±100gf
 Operating Stroke: 2.0mm±0.3
 Protection Grade: IP65, IK08
 Function: (ON)-OFF
 Contact: Silver Alloy
 Base: PBT
 Shell: Brass, Ni Plating
 Button: SUS
 Terminal: Brass, silver
 Lamp Type: LED
 Lamp Life: 50000H
 Rating (Resistive load): 5A 250V AC
 Contact Resistance: 50mΩ MAX.
 Insulation Resistance: 100MΩ MIN.
 Dielectric Strength: 1500V AC 1 minute
 Electrical life: 50,000 cycles
 Mechanical life: 200,000 cycles
 Operating Temperature: -20°C~80°C
 Relative Air Humidity: 45%~85%
 Safety Approval:



公差 TOLERANCES .X±0.5 .XX±0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECON NO.	版本 VERSION	核准 APPROVED BY	比例尺 SCALE	核对 CHECKED BY	日期 DATE	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
				A0		1:1		2021.04.27	孙成	PBM-19M12-FT-RW2-R12-B8S-A3	PBM-19M12-FT-RW2-R12-B8S-A3_A0