


RoHS




SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list				
ITEM	PC	PB	PA	L
Alternate	3.00	16.00	4.00	23.00
Alternate				

深圳市连盛精密连接器有限公司

PART NO.

PH-01519

TITLE:

2.0PH 2H=2X2.0 2X4P DIP PA6T

OPERATION

DRAW

SCALE

FIT

X.X ±0.30

CHECK

UNIT

mm

X.XX ±0.20

SIZE

A4

X.XXX ±0.10

APPROVE

SHEET

1/1

Angle ±3°

PROJ.

A0 2012.04.11 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION CHANGE

DIM TOL