


● ELECTRICAL PARAMETERS

谐振器产品技术指标		Min	Max	Units
1.Holder Type(型号规格)		SEAM 308		
3. Frequency (标称频率)		76.800		KHz
4.Load Capacitance (CL) (负载电容)		12.5		pF
5.Drive Level (激励功率)		1.000		uw
6.Equivalent Resistance (谐振电阻)			30	KΩ
7.Shunt Capacitance (Co) (静态电容)		0	1.7	pF
8.Motional Capacitance (C1) (动态电容)		0.0028		fF
9.Frequency Tolerance at 25°C (调整频差)		-20	20	ppm
10.Temperature Coefficient 二次温度系数		[-0.035±0.01]ppm/°C		
11.Insulation Resistance (at DC 100V) (绝缘电阻)		500		MΩ
12.Operating Temperature Range (工作温度范围)		-20	70	°C
13. Storage Temperature Range (储存温度范围)		-40	85	°C
14. Aging (老化率)		± 5		ppm/year
15. DLD2	N/A		N/A	Ω
16. FLD2			N/A	ppm
17. RLD2			N/A	Ω
18. SPDB			N/A	db
19. Other(其它)		N/A		

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)



FREQUENCY VS. TEMPERATURE CURVE

