




| Rev. | ECN Number | Description | Date | Drawn | Checked | Approved |
|------|------------|-------------|------|-------|---------|----------|
| | | | | | | |

技术要求:

1. 材质: 不锈钢 SUS301, T=0.10±0.005;
2. 端子锡脚焊接面和接触面不可有毛边, 其他部位毛边最大 0.03mm;
3. 扭曲: 4.5°/1000mm, 拱形 5mm/1000mm;
4. 标示有“▼”符号的为重点控制和检验尺寸;
5. 未标注之 R MAX R0.13;
6. 电镀须满足 48 小时盐雾测试;
7. 寿命测试 > 2 万次, 产品弹力要求在 60gf ~ 80gf 之间
8. 镀底 50 ~ 80U"min, 产品外表面镀全 1U"MIN



| | | | | | | | | | | | | | | | |
|--|--|---|--|------------------------------------|--|---------------------------|--|----------------------|--|-------------------------|--|--|--|--------------|--|
| | | GENERAL TOLERANCE XX: ±0.50 X: ±0.35 .X: ±0.25 .XX: ±0.15 | | SCALE: 1:1 UNIT: mm SIZE: A4 | | DRAWN CHECK APPROVE | | DATE DATE DATE | | DWG. NO. 681-0022B-2 | | TITLE 客户图 RF Antenna Spring, SMT, L3.5*W1.5*H2.2mm | | REV. A | |
| 深圳市蝙蝠无线科技有限公司 Shenzhen bats wireless co., LTD | | | | | | | | | | | | | | SHEET 1/1 | |