







Rev.	ECN Number	Description	Date	Drawn	Checked	Approved



技术要求:

1. 材质: 不锈钢 SUS301, T=0.10±0.005;
2. 端子锡脚焊接面和接触面不可有毛边, 其他部位毛边最大 0.03mm;
3. 扭曲: 4.5°/1000mm, 拱形 5mm/1000mm;
4. 标示有“▼”符号的为重点控制和检验尺寸;
5. 未标注之 R MAX R0.13;
6. 电镀须满足 48 小时盐雾测试;
7. 寿命测试 > 2 万次, 产品弹力要求在 60gf ~ 80gf 之间
8. 镀底 50 ~ 80u"min, 产品外表面镀全 1u"MIN

		GENERAL TOLERANCE		SCALE:	DATE	DWG. NO.	TITLE	REV.
		XX: ±0.50	X: ±2.0°	1:1	DATE	681-0026B-2	客户图	A
X: ±0.35		UNIT: mm		CHECK	DATE	RF Antenna Spring, SMT,		SHEET
.X: ±0.25		SIZE: A4		APPROVE	DATE	L2.8*W1.55*H1.1mm		1/1
.XX: ±0.15						PARTS NO. (INTENDED USE)		
						BWO026BG+12.8W1.55H1.1		
深圳市蝙蝠无线科技有限公司		Shenzhen bats wireless co., LTD						