







| Rev. | ECN Number | Description | Date | Drawn | Checked | Approved |
|------|------------|-------------|------|-------|---------|----------|
|      |            |             |      |       |         |          |



焊接尺寸  
尺寸公差 ±0.05

技术要求:

1. 材质: 不锈钢 SUS301, T=0.10±0.005;
2. 端子锡脚焊接面和接触面不可有毛边, 其他部位毛边最大 0.03mm;
3. 扭曲: 4.5°/1000mm, 拱形 5mm/1000mm;
4. 标示有“ ”符号的为重点控制和检验尺寸;
5. 未标注之 R MAX R0.13;
6. 电镀须满足 48 小时盐雾测试;
7. 寿命测试 > 2 万次, 产品弹力要求在 60gf ~ 80gf 之间
8. 镀底 50 ~ 80U"min, 产品外表面镀全 1U"MIN

|  |           |            |          |         |      |  |       |          |   |       |      |      |  |
|--|-----------|------------|----------|---------|------|--|-------|----------|---|-------|------|------|--|
| GENERAL TOLERANCE                                |           | SCALE: 1:1 |          | DRAWN   |      | DATE   |       | DWG. NO. |   | TITLE |      | REV. |  |
| XX ±0.50   | X ±0.35   | X ±2.0°    | UNIT: mm | CHECK   | DATE | 681-0032A-2  | 客户图   |          | RF Antenna Spring, SMT,<br>L3.5*W1.0*H2.5mm |       | A    |      |  |
| .X ±0.25   | .XX ±0.15 | .X ±1.0°   | SIZE: A4 | APPROVE | DATE | PARTS NO. (INTENDED USE)<br>BWM0032AG-L3.5W1.0H2.5 | SHEET |          | 1/1   |       | REV. |      |  |
|  |           |            |          |         |      |  |       |          |   |       |      |      |  |
| 深圳市蝙蝠无线科技有限公司<br>Shenzhen bats wireless co., LTD |           |            |          |         |      |  |       |          |   |       |      |      |  |