






Rev.	ECN Number	Description	Date	Drawn	Checked	Approved



焊接尺寸

尺寸公差 ±0.05



技术要求:

1. 材质: 不锈钢 SUS301, T=0.10±0.005;
2. 端子锡脚焊接面和接触面不可有毛边, 其他部位毛边最大 0.03mm;
3. 扭曲: 4.5°/1000mm, 拱形 5mm/1000mm;
4. 标示有“▼”符号的为重点控制和检验尺寸;
5. 未标注之 R MAX R0.13;
6. 电镀须满足 48 小时盐雾测试;
7. 寿命测试 > 2 万次, 产品弹力要求在 60gf ~ 80gf 之间
8. 镀底 50 ~ 80u"min, 产品外表面镀全 1u"MIN

GENERAL TOLERANCE		SCALE: 1:1		DRAWN		DATE		DWG. NO.		TITLE		REV.	
XX ±0.50	X ±0.35	X ±0.25	XX ±0.15	UNIT: mm	CHECK	DATE	DATE	681-0033B-2	客户图		A		
X ±2.0	X ±1.0	X ±0.5	XX ±0.15	SIZE: A4	APPROVE	DATE	DATE	PARTS NO. (INTENDED USE) BMW0033BG-L3.4W0.9H2.0	RF Antenna Spring, SMT, L3.40*W0.9*H2.0mm		SHEET 1/1		



深圳市蝙蝠无线科技有限公司
Shenzhen bats wireless co., LTD