

REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD




SPECIFICATIONS

Electrical

Current Rating: 1.5A AC(rms)/DC
 Contact Resistance: 20 mΩ Max
 Insulation Resistance: 1000 MΩ Min
 Withstanding Voltage: 500V AC r.m.s
 Temperature Range—Operating: -40°C~+105°C

Material and Plating

Housing: PA66 UL94V-0 , Black
 Contact: Phosphor Bronze, Gold Plated Over Nickel



SECTION A-A

 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 18/JUN/13	PART NO. FR-1YF-06	ITEM NO. FR-1YF-06	 Leader Of Industry
	DESIGN UNITS Inch (metric)	X.±.012(0.30)	X.*±5'	CHECKED BY CHERRY	DATE 18/JUN/13	TITLE MINI JUMPER PITCH: .079"(2.00mm)	
SCALE 5:1	SIZE A4	X.XX±.006(0.15)	.XX±1"	DRAWN BY KATE	DATE 18/JUN/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
						REV 0	SHEET NO. 1/1