



Dimensions:mm

A:12.0 ± 0.5

B:12.0 ± 0.5

C:8.0 (Max)

Part No.	Inductance	TESTING	DC	RATED DC
	L (uH)	FREQ (KHZ)	RESISTANCE (OHM)Max	CURRENT (A)Max
CDRH127N-1R2□	1.2	200	7.0m	9.80
CDRH127N-2R4□	2.4	200	11.5m	8.00
CDRH127N-3R5□	3.5	200	13.5m	7.50
CDRH127N-4R7□	4.7	200	15.8m	6.80
CDRH127N-6R1□	6.1	200	17.6m	6.60
CDRH127N-7R6□	7.6	200	20.0m	5.90
CDRH127N-100□	10	200	21.6m	5.40
CDRH127N-120□	12	200	24.3m	4.90
CDRH127N-150□	15	200	27.0m	4.50
CDRH127N-180□	18	200	39.2m	3.90
CDRH127N-220□	22	200	43.2m	3.60
CDRH127N-270□	27	200	45.9m	3.40
CDRH127N-330□	33	200	64.8m	3.00
CDRH127N-390□	39	200	72.9m	2.75
CDRH127N-470□	47	200	0.100	2.50
CDRH127N-560□	56	200	0.110	2.35
CDRH127N-680□	68	200	0.140	2.10
CDRH127N-820□	82	200	0.160	1.95
CDRH127N-101□	100	200	0.220	1.70
CDRH127N-121□	120	200	0.250	1.60
CDRH127N-151□	150	200	0.280	1.42
CDRH127N-181□	180	200	0.350	1.30
CDRH127N-221□	220	200	0.390	1.16
CDRH127N-271□	270	200	0.560	1.06
CDRH127N-331□	330	200	0.640	0.95
CDRH127N-391□	390	200	0.700	0.88
CDRH127N-471□	470	200	0.980	0.79
CDRH127N-561□	560	200	1.070	0.73
CDRH127N-681□	680	200	1.460	0.67
CDRH127N-821□	820	200	1.640	0.60
CDRH127N-102□	1000	200	1.820	0.55

□:K=±10% M=±20% P=±30%