



**SPECIFICATIONS**

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material:Wafer Nylon46,UL94V-0  
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
1.25-2AW	1.25	4.25
1.25-3AW	2.50	5.50
1.25-4AW	3.75	6.75
1.25-5AW	5.00	8.00
1.25-6AW	6.25	9.25
1.25-7AW	7.50	10.50
1.25-8AW	8.75	11.75
1.25-9AW	10.00	13.00
1.25-10AW	11.25	14.25
1.25-11AW	12.50	15.50
1.25-12AW	13.75	16.75
1.25-13AW	15.00	18.00
1.25-14AW	16.25	19.25
1.25-15AW	17.50	20.50
1.25-16AW	18.75	21.75

**PCB LAYOUT**

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	1.25-NAW		版本 REV.	A				
			X.±0.25	X.*±2'		2013、07、01	张名		品名 TITLE	1.25弯针		页次 SHEET	1/1			
			.X±0.20	.X*±1'						2013、07、03			张名	客户料号 CUTL. NO.	WAFER DIP TYPE	
			.XX±0.15	.XX*±0.5'											2013、07、05	张名
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1											

联系电话 18058866958