

### **SPECIFICATIONS**

#### Mechanical

Contact Retention Force: 0.21Kg(0.44Lb)min.

Durability: 100 Cycles

### **Electrical**

Voltage Rating: 120V Current Rating: 0.5A

Contact Resistance:  $35m\Omega$  max.

**Dielectrical Withstanding Voltage:** 300V **Insulation Resistance:**  $500M\Omega$  min.


# **Physical**

Housing: LCP, UL 94-0, Black Contact: Phosphor Bronze


Plating: See "ORDERING INFORMATION"
Operating Temperature: -55 ℃ to +85 ℃

#### SFP CONNECTOR

3S Series, SFP(Small Form-Factor Pluggable) standard type, 1x1, 0.8mm pitch



### **DRAWING**



## ORDERING INFORMATION

