






MAPX	MODIFICATION	DATE



备注

1. 材质:
 - 1.1 胶芯材质: PBT/LCP ;
 - 1.2 端子材质: C2680R-H; T=0.20mm;
 - 1.3 外壳材质: SPCC; T=0.35mm;
2. 处理:
 - 2.1 端子镍底50u", 镀锡100u";
接触部份按客户要求镀金;
 - 2.2 外壳镀镍100u"以上;
3. 电气:
 - 3.1 额定电流: 1AMP;
 - 3.2 绝缘阻抗: 1000MΩ MIN;
 - 3.3 接触阻抗: 30 MILLIOHMS MAX;
 - 3.4 耐电压: AC 500V FOR 1 MINUTE;
 - 3.5 工作温度: -40° C至+105° C;
4. 胶芯PBT, 白胶料号: AMB2DNIATX-3401
 胶芯PBT, 黑胶料号: AMB3DNIATX-3401
 胶芯LCP, 本色料号: AMB1DNIATX-3401
 胶芯LCP, 黑色料号: AMB9DNIATX-3401

1 1u"	5 15u"
2 3u"	6 30u"
3 5u"	7 50u"
4 10u"	

傲踢u"杆

产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司						
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.	917-511A1015B20200	
X.	±0.25	X.	±5°	比例 SCALE	1:1	审核 CHKD		产品名称 PRODUCT NO.	AM4代E款白胶1U两脚焊接式	
.X	±0.20	.X	±2°	日期 DATE	2012.04.02	核准 APPD		角法 VIEW	版本 VER	AO
.XX	±0.15	.XX	±1°							
.XXX	±0.10	.XXX	±0.5°							