





MAPX	MODIFICATION	DATE

NOTES:  
Housing: Thermoplastics  
Contact: Copper Alloy  
Shell: Copper Alloy/Steel  
Voltage Current Rating:1.5 AMP. 30V AC  
Insulation Resistance:1000MΩ Min.  
Contact Resistance:30 MΩ Max.  
Dielectric Withstanding Voltage:500W AC  
Temperature Range:-55°C to +85°C  
Insulator color: Black/White  
Plastic material:PBT/LCP  
Shell finish:Nickel plated/Tin-Lead plated  
Contact finish:  
01:Selective Gold Flash  
02:Selective Gold 3U"  
03:Selective Gold 5U"  
04:Selective Gold 15U"  
05:Selective Gold 30U"



<b>产品图</b> <b>PRODUCT CHART DWG</b> 公差一览表 <b>TOLERANCE UNLESS OTHERWISE</b>				<b>深圳市精拓金电子有限公司</b>					
单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.	917-141B101AAX0200				
.X	±0.25	.X	±5.°	产品名称 PRODUCT NAME	AM A款一体式双卡点无脚铁壳反向				
.X	±0.20	.X	±2.°	产品图号 PRODUCT NO.	PBT白胶1U 17MM				
.XX	±0.15	.XX	±1.°	角法 VIEW		版本 VER	AO		
.XXX	±0.10	.XXX	±0.5°	日期 DATE	2012.12.25	核准 APPD			