

MAPX	MODIFICATION	DATE



Specification:

1. Electrical Characteristics:  
 Dielectric Withstanding Voltage: AC 500V/1MINUTE.  
 Insulation Resistance: 1000 MΩ/Min.  
 Contact Resistance: 30 mΩ Max.

2. Mechanical Characteristics:  
 INSERTION FORCE: 30N (3.06Kgf) MAX  
 EXTRACTION FORCE: 10~30N (1.02~3.06Kgf)  
 Durability: 1500cycles. EXTRACTION FORCE: 10~30N (1.02~3.06Kgf)

3. Material:  
 Terminal: Phosphor Bronze, C2680R-EH T=0.25  
 Plating: Gold 0.76 um Min plating over 1.27 um Min Nickel underplate, 2.54 um Min Sn selective plating on solder tail;  
 Shell: Bronze, SPCCR-H =0.30mm  
 Plating: Nickel underplate 2.54 um Min;  
 Housing: PBT white

4. Environmental:  
 Operating Temperature: 0° C to +85° C.



<b>产品图</b> PRODUCT CHART DWG		<b>深圳市精拓金电子有限公司</b>								
公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.	906-862A2028D10200			
X.	±0.25	X.	±5.°	比例 SCALE	1:1	审核 CHKD	产品名称 PRODUCT NO. AF10.0侧插短体外鱼叉内O型脚无边铜壳加厚1.5LCP黑胶			
.X	±0.20	.X	±2.°	日期 DATE	2014.02.20	核准 APPD	角法 VIEW		版本 VER	AO
.XX	±0.15	.XX	±1.°							
.XXX	±0.10	.XXX	±0.5°							