



|                   |                             |                   |
|-------------------|-----------------------------|-------------------|
| 目錄<br><b>MAPX</b> | 設變內容<br><b>MODIFICATION</b> | 日期<br><b>DATE</b> |
|                   |                             |                   |

NOTES:  
 Housing: Thermoplastics,UL94V-0  
 Contact: Copper Alloy  
 Shell: Copper Alloy/Steel  
 Voltage Current Rating:1.5 AMP. 30V AC  
 Insulation Resistance:1000MΩ Min.  
 Contact Resistance: 30 MΩ Max.  
 Dielectric Withstanding Voltage:500W AC  
 Temperature Range: -35°C to +85°C  
 Insulator color: Black/White  
 Plastic material:PBT/LCP/Others  
 Shell finish:Nickel plated/Tin-Lead plated  
 Mechanical:  
 Mating Force:3.5KG MAX  
 Unmating Force:0.7 KG MIN.  
 Contact finish:  
 01: Selective Gold Flash  
 02: Selective Gold 3U"  
 03: Selective Gold 5U"  
 04: Selective Gold 15U"  
 05: Selective Gold 30U"

|                                     |       |       |       |              |     |               |       |                          |                          |            |            |
|-------------------------------------|-------|-------|-------|--------------|-----|---------------|-------|--------------------------|--------------------------|------------|------------|
| 产品图<br>PRODUCT CHART DWG            |       |       |       | 深圳市精拓金电子有限公司 |     |               |       |                          |                          |            |            |
| 公差一览表<br>TOLERANCE UNLESS OTHERWISE |       |       |       | 单位<br>UNITS  | MM  | 制图<br>DRAWING | Z-Y-B | 产品料号<br>PRODUCT PART NO. | 916-362A1014Y10201       |            |            |
| X.                                  | ±0.25 | X'    | ±5'   | 比例<br>SCALE  | 1:1 | 审核<br>CHKD    | 雷永键   | 产品名称<br>PRODUCT NO.      | AF10.0短体180度鱼叉脚无边铜壳PBT白胶 |            |            |
| .XX                                 | ±0.15 | .XX'  | ±1'   |              |     |               |       |                          | 日期<br>DATE               | 2013.05.10 | 核准<br>APPD |
| .XXX                                | ±0.10 | .XXX' | ±0.5' |              |     |               |       |                          |                          |            |            |