



MAPX	MODIFICATION	DATE

SECTION A-A

RECOMMENDED PCB LAYOUT

PCB图仅供参考

- Note:
1. Material:
 - 1.1 Housing: High temperature thermoplastic with g.f,UL94v-0
 - 1.2 Contact: copper alloy,t=0.20mm
 - 1.3 Shell: copper alloy or SUS,t=0.25mm
 2. Specification:
 - 2.1 Current rating:1,5PIN 1.8A Max/2,3,4PIN 1A Max.
 - 2.2 Dielectric withstanding voltage: 100 V(ac) for 1 min.
 - 2.3 Contact resistance: 30 mΩ Max.
 - 2.4 Insulation resistance: 100 MΩ Min.
 - 2.5 Total mating force: 3.57 Kgf Max.
 - 2.6 Total unmating force: 1.0 Kgf Min.
 - 2.7 Temperature range: -30°C~80°C

???	深圳市精拓金电子有限公司				
PRODUCT CHART DWG	??	MM	??	YANG	920-A62A2021S10106
?????	UNITS		DRAWING	PRODUCT PART NO.	920-A62A2021S10106
TOLERANCE UNLESS OTHERWISE	??	1:1	CHKD	PRODUCT NO.	MICRO 5P-F B型四脚插板7.2无卷
X. ±0.30 X. ±5.°	SCALE		APPD	VIEW	边无柱端子加长0.75
.X ±0.25 .X ±2.°	DATE	2019.11.23	???	??	??
.XX ±0.20 .XX ±1.°				VER	AD
.XXX ±0.10 .XXX ±0.5°					