



RoHS

MAPX

MODIFICATION

DRW





DATE



P. C. B LAYOUT T=1.20mm TOL:±0.05

Specifications:

1. Current Rating: 1.0A at 30V AC.
2. Withstanding Voltage: 100V AC for one minute.
3. Insulation Resistance: 100MΩ Min.
4. Contact Resistance: 30mΩ Max.
5. Mating Force: 3.57kgf Max.
6. Unmating Force: 1.02kgf Min.
7. Operating Temperature: -25°C ~ +85°C.



4	5P端子	C5191		GOLD/TIN PLATED
3	4P端子	C5191		GOLD/TIN PLATED
2	主体	LCP	BLUE	UL 94V-0
1	外壳	C2680		NICKEL/GOLD PLATED
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

<p>产品图 PRODUCT CHART DWG</p> <p>公差一览表 TOLERANCE UNLESS OTHERWISE</p> <table border="1"> <tr> <td>X.</td> <td>±0.25</td> <td>X.</td> <td>±5.°</td> </tr> <tr> <td>.X</td> <td>±0.20</td> <td>.X</td> <td>±2.°</td> </tr> <tr> <td>.XX</td> <td>±0.15</td> <td>.XX</td> <td>±1.°</td> </tr> <tr> <td>.XXX</td> <td>±0.10</td> <td>.XXX</td> <td>±0.5°</td> </tr> </table>				X.	±0.25	X.	±5.°	.X	±0.20	.X	±2.°	.XX	±0.15	.XX	±1.°	.XXX	±0.10	.XXX	±0.5°	<p>深圳市精拓金电子有限公司 Shenzhen Jing Tuo Jin Electronics Co., Ltd.</p>					
X.	±0.25	X.	±5.°																						
.X	±0.20	.X	±2.°																						
.XX	±0.15	.XX	±1.°																						
.XXX	±0.10	.XXX	±0.5°																						
单位 UNITS	MM	制图 DRAWING	尹先华	制图料号 PRODUCT PART NO.	916-862A205EY10200																				
比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	USB AF 3.0立式11.6夹板脚无边不锈钢蓝胶SMT																				
日期 DATE	2021-04-14	核准 APPD	黄国荣	角法 VIEW	版本 VER	AO																			