



D1 = 3.0
D2 = 3.8
D3 = 4.5
D4 = 5.5

MAPX	MODIFICATION	DATE

ELECTRICAL
 Current rating:1Amp
 Dielectric withstanding voltage:
 AC 250v min(for 1 minute)
 Insulation resistance:
 1000MΩ min(at 500v DC)
 Contactresistance:
 30mΩ max
 Durabil tty:2500 cycles
 Working temperature:-55° C~+105° C
 标注"▲"的为重点管控尺寸

MECHANICAL
 Insulator material:
 PBT&glass-fiber reinforced UL 94-H
 Contact: Brass
 Housing color: white
 Shell: nickel(ortin,gold)plated
 Number of contact:04.
 Durabil tty:2500 cycles

- NOTE:
 1. 材质: SPCC T= ≥0.30mm。
 2. 电镀: 铜底 100U" 镍底 100U" 盐雾测试24H &12H
 3. 产品表面无明显毛边, 压痕, 划伤等现象。

产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司								
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	尹先华	制图料号 PRODUCT PART NO.	917-781A101AD60201	
X.	±0.25	X.	±5.°	比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	AM 三件式36mm铁壳48H白胶 OD4.5	
.XX	±0.15	.XX	±1.°	日期 DATE	2021-04-15	核准 APPD	黄国荣	角法 VIEW	版本 VER	AO
.XXX	±0.10	.XXX	±0.5°							